

TECHSPEC®

25mm Dia., Enhanced Aluminum, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-579** 3-5 DAYS

- 1 +

A\$211.20

ADD TO CART

Qty 1-5

A\$211.20

Qty 6+

A\$168.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 $\lambda/10$

Substrate: Fused Silica (Corning 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 450 - 650
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View