

TECHSPEC®

25mm Dia. High Performance Glass Linear Polarizer



Stock #47-216

In Stock

-

1

+

A\$302.40

ADD TO CART

Qty 1-5

A\$302.40

Qty 6+

A\$241.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

AR: R_{avg} <0.5% @ 400 - 700nm

Diameter (mm):

25.00

Extinction Ratio:

10,000:1

Substrate: ☐

Polymer Film between B270
Operating Temperature (°C): -25 to +65
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): 25 (for random polarization)
Transmission Tolerance (%): ±2
Type: Linear Polarizer
Parallelism (arcmin): <4
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Dichroic Polarizing Film between Glass
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): <1λ
Polarization Axis Mark (°): ±2

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View