

25mm Dia. Left-Handed VIS-Coated Glass Circular Polarizer (CP42HE)



Stock #19-935 3-5 DAYS

- 1 +

A\$96.00

ADD TO CART

Qty 1-9
A\$96.00
Qty 10+
A\$86.40
Volume Pricing
Request Quote

Get Product Downloads



Coating:
VIS AR Coated

Diameter (mm):
25.00

Substrate: [Polymer Film CP42HE](#) Laminated Between Glass

Operating Temperature (°C):

-40 to +80
Thickness (mm): 2.00 ±0.10
Transmission (%): 45 ±2
Type: Left-Handed Circular Polarizer
Dimensional Tolerance (mm): ±0.20
Construction: Laminated Glass Polarizing Film
Coating Specification: R _{avg} <0.5% @ 425 - 700nm
Wavelength Range (nm): 425 - 700
Polarization Efficiency (%): >99.90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant