



TECHSPEC® 25mm Dia., VIS Broadband Dielectric, λ /10 Stemmed Mirror



Stock **#16-734** CLEARANCE 3-5 DAYS

- 1 + **A\$252.80**

ADD TO CART

Qty 1-5

A\$252.80

Qty 6+

A\$202.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 λ /10

Substrate:  Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R_{avg} ≥98% @400 - 750nm (0 - 45°, All Polarizations) R_{avg} ≥99% @400 - 750nm (0 - 45°, S-Polarization)
Coating: Dielectric Mirror (400-750nm)
Coating Type: Dielectric
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 400 - 750
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20
Damage Threshold, Reference:  0.5J/cm², 20ns, 20Hz @532nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View