

TECHSPEC® 22mm CA, 100mm FL, Mounted MgF₂ Coated Achromatic Doublet Lens



TECHSPEC® Mounted MgF₂ Coated Achromatic Lenses

Stock #13-009 CLEARANCE 3-5 DAYS

-

1

+

A\$164.72

ADD TO CART

Qty 1+

A\$164.72

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: ☐
[N-BK7](#) / [N-SF5](#)

f/#:
4.00

Numerical Aperture NA:
0.13

Coating:

MgF ₂ (400-700nm)
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700
Back Focal Length BFL from Housing (mm): 90.66
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 22.0
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Edge Thickness ET (mm): 6.61
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±2
Radius R₁ (mm): 61.47
Radius R₂ (mm): -44.64
Radius R₃ (mm): -129.94
Surface Quality: 40-20
Lens Included: #32-327
Mount Included: #56-354
Mount Diameter (mm): 30.0
Extension Length (mm): 24.2
Total Length (mm): 28.2
Thread Type: C-Mount
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View