

TECHSPEC® 25mm Dia. x 100mm FL, Uncoated, Ge Plano-Convex Lens



Stock **#69-643** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$520.00

ADD TO CART

Qty 1-5
A\$520.00
Qty 6+
A\$416.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00 @ 10.6µm

Back Focal Length BFL (mm):
99.25

Coating: Uncoated
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.74
Radius R₁ (mm): 300.39
Clear Aperture CA (mm): 24
f#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 2000 - 14000

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View