

TECHSPEC® 25mm Dia x 125mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #47-744 3-5 DAYS

-

1

+

A\$112.00

ADD TO CART

Qty 1-5

A\$112.00

Qty 6+

A\$89.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
125.00

Substrate:

N-BK7

f/#:

5
Numerical Aperture NA: 0.1
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 123.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.78
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 64.60
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View