

TECHSPEC® 25mm Dia x 150mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-019** 3-5 DAYS

- 1 + **A\$112.00**

ADD TO CART

Qty 1-5
A\$112.00
Qty 6+
A\$89.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
150.00

Substrate:
[N-BK7](#)

f/#:

6
Numerical Aperture NA: 0.08
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 147.70
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 2.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 77.78
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View