

TECHSPEC®

25mm Dia. x 25mm FL, Uncoated, Si Plano-Convex Lens



Stock **#69-673** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$344.00

ADD TO CART

Qty 1-5
A\$344.00
Qty 6+
A\$275.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
25.00 @ 10.6µm

Back Focal Length BFL (mm):
23.98

Coating: Uncoated
Substrate: ☐ Silicon (Si)
Surface Quality: 60-40
Power (P-V) @ 632.8nm: 2λ
Irregularity (P-V) @ 632.8nm: λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 3.50 ±0.10
Edge Thickness ET (mm): 2.19
Radius R₁ (mm): 60.44
Clear Aperture CA (mm): 24
f#: 1.00
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1200 - 7000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View