

TECHSPEC®

25mm Dia. x 75mm FL VIS-EXT, Inked, Double-Convex Lens



Stock **#89-180-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 +

A\$96.00

ADD TO CART

Qty 1-9
A\$96.00
Qty 10+
A\$86.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Back Focal Length BFL (mm):
73.84

Effective Focal Length EFL (mm):

75.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.45
Radius R₁=R₂ (mm): 76.66
Clear Aperture CA (mm): 24.00
f/#: 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View