

TECHSPEC® 25mm Dia x -100mm FL, Protected Gold, Convex Mirror



Convex Mirrors

Stock **#87-691** 3-5 DAYS



1



A\$99.20

ADD TO CART

Qty 1-5

A\$99.20

Qty 6+

A\$79.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-100.00

Center Thickness CT (mm):
3.00

Clear Aperture (%): 90.00
Coating: Protected Gold (700-10000nm)
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 2.61
Focal Length Tolerance (%): ±2
Radius R (mm): 200.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 700 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant