

TECHSPEC® 25mm Dia x -150mm FL, Protected Silver, Convex Mirror



Convex Mirrors

Stock **#87-681** 3-5 DAYS



1



A\$91.20

ADD TO CART

Qty 1-5

A\$91.20

Qty 6+

A\$72.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-150.00

Center Thickness CT (mm):
3.00

Clear Aperture (%): 90.00
Coating: Protected Silver (450-10000nm)
Coating Specification: R_{avg} >98% @ 450 - 2000nm R_{avg} >98% @ 2000 - 10,000nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 2.74
Focal Length Tolerance (%): ±2
Radius R (mm): 300.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 500 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant