


25mm Diameter Medium Elliptical Holographic Diffuser Kit



Holographic Diffusers



Stock **#53-873** [CONTACT US](#)

− 1 +

A\$932.00

ADD TO CART

Qty 1+

A\$932.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diffusing Angle (°):
2 x60, 5 x30, 10 x60, 20 x80

Diameter (mm):
25.00 ±0.1

Number of Diffusers:
4.00

Operating Temperature (°C):
-30 to +100 (Maximum of 240 Hours)

Substrate: ☐
Polycarbonate

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
