

TECHSPEC[®] 25mm Diameter x 75mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-173 CLEARANCE 3-5 DAYS

-

1

+

A\$175.92

ADD TO CART

Qty 1+

A\$175.92

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f/#:
3.00

Numerical Aperture NA:
0.17

Coating: Uncoated	
Type: Cylinder Lens, Plano-Convex	
Wavelength Range (nm): 200 - 2200	
Back Focal Length BFL (mm): 72.60	
Center Thickness CT (mm): 3.50	
Center Thickness Tolerance (mm): ±0.1	
Edge Thickness ET (mm): 1.15	
Focal Length Tolerance (%): ±3	
Radius R (mm): 34.39	
Surface Quality: 40-20	
Wedge Tolerance (arcmin): 15.00	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	