

25mm Fixed Focal Length Lens



#86-210



Stock **#86-208** [CONTACT US](#)

-

1

+

A\$2,859⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$2,859.00 each
Need More?	Request Quote

Product Downloads

General

4/3" Format Fixed Focal Length Lenses	Series:
Fixed Focal Length Lens	Type:

Physical & Mechanical Properties

Variable	Iris Option:
----------	--------------

89.00	Length (mm):
45.0	Maximum Diameter (mm):
45	Outer Diameter (mm):
250.00	Weight (g):

Optical Properties	
40.9	Horizontal Field of View @ Max Sensor Format:
125.00	Field of View @ Min Working Distance (mm):
21.60	Maximum Image Circle (mm):
25.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/2 - f/16	Aperture (f/#):
<-0.6	Distortion (%):
-0.57	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor	
4/3"	Maximum Sensor Format:
5.00	Pixel Size (µm):

Threading & Mounting	
M40.5 x0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TVDistortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.