

25mm FL SWIR Series Fixed Focal Length Lens



Stock #68-688 3-5 DAYS

[Similar Products](#)

⊖ 1 ⊕

A\$3,368.00

ADD TO CART

Qty 1+
A\$3,368.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
150.00

Iris Option:
Variable

Length (mm):
43.00 - 48.4

Filter Thread:
M35.5 x 0.5

Maximum Diameter (mm):
43

Weight (g): 135
Horizontal Field of View, 1" Sensor: 29.3°
Maximum Image Circle (mm): 16.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Maximum Sensor Format: 1"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.4 - f/16
Distortion (%): <-1.0
Lens Wavelength Range: SWIR

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)