

TECHSPEC® 25mm H x 50mm L x 50mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-021** 3-5 DAYS

- 1 + **A\$176.00**

ADD TO CART

Qty 1-5
A\$176.00
Qty 6+
A\$140.80
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate:
[N-BK7](#)

f/#:
2

Numerical Aperture NA:

0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 47.20
Center Thickness CT (mm): 4.24
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.93
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View