

TECHSPEC®

25mm H x 50mm L x -25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #68-061

3-5 DAYS

-

1

+

A\$172.80

ADD TO CART

Qty 1-5

A\$172.80

Qty 6+

A\$137.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-25.00

Substrate: ☐
[N-SF11](#)

Coating:
Uncoated

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 2500
Back Focal Length BFL (mm): -27.24
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 8.25
Focal Length Tolerance (%): ±3
Radius R ₁ (mm): -19.62
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View