

[See all 21 Products in Family](#)

**TECHSPEC® 25mm, M40 Mount, CA Series Fixed Focal Length Lens**



25mm, M40 Mount, CA Series Fixed Focal Length Lens



Stock #29-259 **20+ In Stock**

⊖ 1 ⊕ A\$1,320<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	A\$1,320.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

CA Series **Product Family:**

Fixed Focal Length Lens **Type:**

High Performance Lens **Imaging Lens Type:**

**Physical & Mechanical Properties**

Variable	<b>Iris Option:</b>
93.65	<b>Length (mm):</b>
52	<b>Maximum Diameter (mm):</b>
52	<b>Outer Diameter (mm):</b>
0	<b>Maximum Rear Protrusion (mm):</b>

## Optical Properties

50.0°	<b>Horizontal Field of View, APS-C Sensor:</b>
38.0°	<b>Horizontal Field of View, 4/3" Sensor:</b>
32.1°	<b>Horizontal Field of View, 1.1" Sensor:</b>
29.2°	<b>Horizontal Field of View, 1" Sensor:</b>
20.2°	<b>Horizontal Field of View, 2/3" Sensor:</b>
27.90	<b>Maximum Image Circle (mm):</b>
0.019	<b>Numerical Aperture NA, Object Side:</b>
10 (9)	<b>Number of Elements (Groups):</b>
25.00	<b>Focal Length FL (mm):</b>
200 - ∞	<b>Working Distance (mm):</b>
<b>FOV @ Max Sensor Format, H x V (mm):</b>	
Horizontal: 50.0°	
Vertical: 38.0°	
Diagonal: 61.5°	
f/2.8 - f/16	<b>Aperture (f#):</b>
λ/4 MgF <sub>2</sub>	<b>Coating:</b>
λ/4 MgF <sub>2</sub>	<b>Coating Specification:</b>
39.64	<b>Entrance Pupil Position (mm):</b>
47.46	<b>Object Space Principal Plane (mm):</b>
-8.15	<b>Image Space Principal Plane (mm):</b>
5.8	<b>Maximum Distortion (%):</b>
-56.88	<b>Exit Pupil Position (mm):</b>
VS	<b>Lens Wavelength Range:</b>

## Sensor

APS-C	<b>Maximum Sensor Format:</b>
2.74	<b>Pixel Size (μm):</b>

## Threading & Mounting

M52 x 0.75 (Female)	<b>Filter Thread:</b>
M40 x 0.75	<b>Mount:</b>

## Environmental & Durability Factors

-20 to +60 For questions regarding operating temperature please contact our support team	<b>Storage Temperature (°C):</b>
--	----------------------------------

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

---

## Product Details

- APS-C (27.9mm), TFL-Mount Lens or M40 Mount Lens
- Greater than 30 MegaPixels, 3.45µm Pixel Size Sensors
- High Resolution, Compact APS-C Lens (CA)
- 35mm to 100mm Focal Length

TECHSPEC® CA (Compact APS) Series Fixed Focal Length Lenses are designed for high-resolution large-format sensors. Covering the APS-C format sensors with a 28mm image circle, these lenses feature a [TFL Mount](#) or M40 Mount. TFL Mounts feature an M35 x 0.75 thread with a 17.5mm flange distance, and offer the same robustness and ease of use as a C-Mount. M40 Mounts feature a M52 x 0.75 thread with a 17.526mm flange and provide a robust, large-format mounting solution ideal for high-resolution and larger image sensors with improved mechanical stability and optical performance compared to smaller format mounts. TECHSPEC® CA Series Fixed Focal Length Lenses offer a compact size while accommodating large format sensors, making them ideal for machine vision and [factory automation](#) applications.

These lenses won the [3rd place 2020 Inspect Award](#) and the [Silver-Level 2020 VSD Innovators Award](#).

---