

TECHSPEC® 25mm NIR, Polarizing Cube Beamsplitter



TECHSPEC® Broadband Polarizing Cube Beamsplitters

Stock #49-872 3-5 DAYS

− 1 +

A\$563.20

ADD TO CART

Qty 1-5

A\$563.20

Qty 6+

A\$450.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcmin):
±3

Clear Aperture (%):
90

Coating Specification:
R_{avg} <0.5% @ 700 - 1100nm

Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Extinction Ratio: 500:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99
Substrate: ☐ N-SF11
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Linear Polarizer
Wavelength Range (nm): 700 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View