

25mm Travel, 0.01mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-731** 5 In Stock

-

1

+

A\$163²⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$163.20 each
Qty 10-24	A\$146.88 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
Mitutoyo	Manufacturer:
w/ Ratchet	Note:
Physical & Mechanical Properties	
	Travel (mm):

25	
	Graduation (mm):
0.01	
	Stem Diameter (mm):
10	
	Stem/Spindle:
Plain/Spherical	
	Stem Length (mm):
15	
	Spindle Diameter (mm):
6.35	
	Min. Spindle Length (mm):
27	
	Max. Diameter (mm):
18	
	Overall Length (mm):
109	

Hardware & Interface Connectivity

	Type of Drive:
Metric Mcrometer	

Regulatory Compliance

	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	REACH 241:
Contains SVHC(s)	

Product Details

- Mcrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

