

## 2.62", English Rotary Stage



Stock #38-193 3-5 DAYS



1



A\$1,715.20

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| A\$1,715.20 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

**Mounting Threads:**  
(4) 6-32 on 1.125" dia. B.C., (4) 1/4-20 on 2.00" dia. B.C.

**Type:**  
English

**Weight (lbs):**  
1.8

**Stage Size (mm):**  
66.5 x 66.5

**Stage Size (inches):**  
2.62 x 2.62

|                                                                        |
|------------------------------------------------------------------------|
| <b>Construction:</b><br>Aluminum top and base; steel tangent arm drive |
| <b>Center Hole:</b><br>0.50" Dia. Thru                                 |
| <b>Travel (°):</b><br>±5 (Fine), 360 (Coarse)                          |
| <b>Type of Drive:</b><br>Tangent Arm                                   |
| <b>Increments (arcmin):</b><br>12                                      |
| <b>Load Capacity, Normal (lbs):</b><br>10                              |
| <b>Load Capacity, Vertical (lbs):</b><br>4                             |
| <b>Type of Movement:</b><br>Rotary                                     |
| <b>Guide System:</b><br>Ball Bearing                                   |
| <b>Table Diameter (inches):</b><br>2.62                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |