

2" x 2" 0.0625mm Dot, Low Reflect Grid Distortion Target



Stock #62-949 3-5 DAYS

1

A\$1,089.60

ADD TO CART

Qty 1-4
A\$1,089.60
Qty 5+
A\$1,035.84
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Low Reflective Chrome

Dot Diameter (mm):
0.0625

Dot Spacing (mm):
0.125

Substrate:
Float Glass

Pattern Size (mm): 25 x 25
Dimensions (inches): 2 x 2 ±0.04
Thickness (mm): 2.00 ±0.2
Center to Center Spacing Tolerance (µm): ± 1
Dot Diameter Tolerance (µm): ±3
NIST Certification: No

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View
