

2X 65mm WD, In-Line Illumination Telecentric Lens



Stock #62-791 3-5 DAYS

- 1 + **A\$1,904.00**

ADD TO CART

Qty 1+
A\$1,904.00

Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
110.00

Ferrule Diameter (inches):
0.312

Horizontal Field of View, 1/2" Sensor:
3.2mm

Horizontal Field of View, 2/3" Sensor:
4.4mm

Maximum Diameter (mm):
17.0

Horizontal Field of View @ Max Sensor Format: 4.4mm
Type: Telecentric Lens
Primary Magnification PMAG: 2X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/16.3
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View