


TECHSPEC® 2X, UV Enhanced Aluminum Canopus® Reflective Beam Expander



TECHSPEC® Canopus™ Reflective Beam Expanders



Stock #37-185 3-5 DAYS

- 1 +

A\$944.00

ADD TO CART

Qty 1-5

A\$944.00

Qty 6+

A\$833.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):

0

Coating:

Enhanced Aluminum (250-700nm)

Design Wavelength DWL (nm): Broadband
Entrance Aperture (mm): 4
Exit Aperture (mm): 8
Expansion Power: 2X
Substrate: Aluminum 6061-T6
Height (mm): 25.4
Length (mm): 71.00
Surface Quality: 40-20
Type: Beam Expander
Weight (g): 133
Width (mm): 38.10
Coating Specification: R_{avg} >89% @ 250 - 450nm R_{avg} >85% @ 250 - 700nm
Wavelength Range (nm): 250 - 700
Style: Fixed Magnification
Surface Roughness (Angstroms): <50 RMS
Wavefront Error, P-V: ≤λ/10 on-axis for a 1mm Dia. Input Beam

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View