

3.0 OD 12.5mm Diameter VUV ND Filter



Stock #20-139 3-5 DAYS

-

1

+

A\$707.20

ADD TO CART

Qty 1-5
A\$707.20
Qty 6+
A\$636.48
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Optical Density OD (Average):
3.0 +0.22/-0.23

Substrate: ☐
UV Grade MgF₂

Coating: Metallic Based ND, with Dielectric Over-Coat
Surface Quality: 40-20
Thickness (mm): 2.00 ±0.10
Transmission (%): 0.10
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 120 - 200
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Parallelism (arcsec): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View