

225mm Max. Aperture, Iris Diaphragm



Stock #70-895 3-5 DAYS

- 1 + **A\$1,235.20**

ADD TO CART

Qty 1-4
A\$1,235.20
Qty 5+
A\$1,091.84
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
12.0

Maximum Aperture (mm):
225.0

Outer Diameter (mm):
300.0

Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 5.00
Lever Length (mm): 40.50
Number of Leaves: 18.00
Thickness (mm): 19.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)