

300mm x 150mm, Breadboard



Stock **#56-937** 20+ In Stock

-

1

+

A\$240^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$240.00 each
Need More?	Request Quote

Product Downloads

General	
	Type:
Metric	
Physical & Mechanical Properties	
	Thickness (mm):
13.00	
	Length (mm):
300.00	
	Width (mm):
150.00	
	Construction:

Black Anodized Aluminum	
0.18mm per 300mm	Flatness (mm):
1.5	Weight (kg):
72.00	Number of Holes:

Threading & Mounting

(72) M6 x 1.0 on 25 Centerline ±0.025mm, on 12.5mm Corners	Mounting Threads:
--	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Provide Stable Platform for Experiments and Test Configurations
- 1/4-20 TPI or M6 Tapped Holes for Various Mounting
- Black Anodized Aluminum

English and Metric Breadboards utilize 1/4"-20, or M6 tapped holes spaced 1" and 25mm apart, respectively, allowing for the creation of customizable benchtop systems. These breadboards are compatible with most optics and photonics mounting solutions. They feature a black anodized finish which reduces reflections from the breadboard and back into the system. English and Metric Breadboards are available in multiple sizes, making it possible to create either compact or large, expansive systems. These breadboards are an ideal platform for any system application.