

TECHSPEC®

30mm, 60mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-524 3-5 DAYS

-

1

+

A\$667.20

ADD TO CART

Qty 1-2

A\$667.20

Qty 3+

A\$581.76

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:

Metric
Stage Size (mm): 30 x 30
Travel (°): ±10
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 2
Mounting Threads: (1) M6 x 1, (8) M2 x 0.4
Radius R (mm): 60
Resolution (arcmin): 5
Stage Size (inches): 1.18 x 1.18
Weight (kg): 0.15

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant