

TECHSPEC® 30mm, Center Drive, Standard Top, 0.25" Travel, English Micrometer



Stock #83-503 **20+ In Stock**

⊖ 1 ⊕ A\$700⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	A\$700.80 each
Qty 3+	A\$611.20 each
Need More?	Request Quote

Product Downloads

General

English Type:

Physical & Mechanical Properties

Linear (X) Type of Movement:

Crossed Roller Bearing Guide System:

Center Drive Drive Orientation:

30mm Standard-Top Stages - Center Drive



30mm Standard-Top Stages - Side Drive



40mm Standard-Top Stages - Center Drive



40mm Standard-Top Stages - Side Drive



70mm Standard-Top Stages - Center Drive



70mm Standard-Top Stages - Side Drive



125mm Standard-Top Stages - Center Drive



125mm Standard-Top Stages - Side Drive

