

TECHSPEC[®] 30mm, Center Drive, Thru-Hole, 0.5" Travel, English Micrometer



Stock #66-395 3-5 DAYS

-

1

+

A\$627.20

ADD TO CART

Qty 1-2

A\$627.20

Qty 3+

A\$547.68

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
English Micrometer

Drive Orientation:
Center Drive

Type: English
Stage Size (mm): 30 x 30
Travel (inches): 0.5
Center Hole: 5/16"-24
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 3
Mounting Threads: (1) 5/16"-24, (6) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
