

TECHSPEC® 3.0mm Dia. x 15.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-425** 3-5 DAYS
[Other Coating Options](#)

- 1 + **A\$75.20**

ADD TO CART

Qty 1-9
A\$75.20
Qty 10+
A\$67.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
3.00 +0.0/-0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Back Focal Length BFL (mm): 14.22
Coating: Uncoated
Substrate: ☐ N-BK7
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.26 ±0.05
Edge Thickness ET (mm): 1.12
Radius R₁ (mm): 7.78
Clear Aperture CA (mm): 2.5
f#: 5
Numerical Aperture NA: 0.10
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
