

TECHSPEC®

30mm, English Micrometer Z-Stage



TECHSPEC® Vertical Translation Stages



Stock #66-495 3-5 DAYS

-

1

+

A\$923.20

ADD TO CART

Qty 1-2

A\$923.20

Qty 3+

A\$806.56

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (Z)

Guide System:
Crossed Roller Bearing

Type of Drive:

English Micrometer
Type: English
Stage Size (mm): 30 x 30
Travel (mm): 5
Center Hole: 1/4-20
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.635
Load Capacity (kg): 1.5
Mounting Threads: (1) 1/4-20, (8) 2-56
Stage Size (inches): 1.18 x 1.18
Straight Line Accuracy (µm): 3

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)