

**TECHSPEC® 30mm, Side Drive, Thru-Hole, 0.25" Travel, Metric Micrometer**



Stock #83-510 3-5 DAYS

- 1 + **A\$627.20**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-2                       |
| A\$627.20                     |
| Qty 3+                        |
| A\$547.68                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Type of Movement:  
Linear (X)

Guide System:  
Crossed Roller Bearing

Type of Drive:  
Metric Micrometer

Drive Orientation:  
Side Drive

|                                                        |
|--------------------------------------------------------|
| <b>Type:</b><br>Metric                                 |
| <b>Stage Size (mm):</b><br>30 x 30                     |
| <b>Travel (mm):</b><br>6.5                             |
| <b>Center Hole:</b><br>5/16"-24                        |
| <b>Construction:</b><br>Aluminium Stage                |
| <b>Leadscrew Pitch (mm):</b><br>0.5                    |
| <b>Load Capacity (kg):</b><br>3                        |
| <b>Mounting Threads:</b><br>(1) 5/16"-24, (6) M2 x 0.4 |
| <b>Stage Size (inches):</b><br>1.18 x 1.18             |
| <b>Straight Line Accuracy (µm):</b><br>2               |
| <b>Pitch (arcsec):</b><br>30                           |
| <b>Yaw (arcsec):</b><br>25                             |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |

---