

TECHSPEC<sup>®</sup> 30R/70T NIR, C-Mounted Plate Beamsplitter



Stock #49-687 [CONTACT US](#)

-

1

+

A\$472.00

ADD TO CART

Qty 1-4

A\$472.00

Qty 5+

A\$414.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating Specification:  
Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region

Construction:  
Plate

Dimensional Tolerance (mm):  
+0.0/-0.25

Extension Length (mm):

|                                                                     |
|---------------------------------------------------------------------|
| 38.0                                                                |
| <b>Housing:</b><br>Black Anodized Aluminum                          |
| <b>Housing Dimension:</b><br>38 x 38 x 50                           |
| <b>Mount:</b><br>C-Mount Enclosure                                  |
| <b>Reflection/Transmission Ratio (R/T):</b><br>30/70                |
| <b>Reflection/Transmission Tolerance (%):</b><br>±5                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-BK7</a> |
| <b>Surface Flatness (P-V):</b><br>1λ                                |
| <b>Surface Quality:</b><br>60-40                                    |
| <b>Thread Type:</b><br>C-Mount (1" x 32 TPI)                        |
| <b>Type:</b><br>Standard Beamsplitter                               |
| <b>Wavelength Range (nm):</b><br>700 - 1100                         |
| <b>Beamsplitter Included:</b><br><a href="#">#49-753</a>            |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |