

## 340nm CWL, 10nm FWHM, 25mm Mounted Diameter



Stock #65-674 CLEARANCE 3-5 DAYS

- 1 + **A\$215.92**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| A\$215.92 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.00 +0.0/-0.2

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥3.0

Clear Aperture CA (mm):  
21.0

Center Wavelength CWL (nm):  
340.00 ±2

|                                                 |
|-------------------------------------------------|
| Center Wavelength CWL Tolerance (nm):<br>±2     |
| Full Width-Half Max FWHM (nm):<br>10.00 ±2      |
| Full Width-Half Max FWHM Tolerance (nm):<br>±2  |
| Minimum Transmission (%):<br>≥25                |
| Operating Temperature (°C):<br>-50 to +75       |
| Coating:<br>Traditional Coated                  |
| Surface Quality:<br>80-50                       |
| Thickness Tolerance (mm):<br>±0.1               |
| Type:<br>Bandpass Filter                        |
| Typical Applications:<br>FURAExcitation         |
| Blocking Wavelength Range (nm):<br>200 - 1200   |
| Construction:<br>Mounted in Black Anodized Ring |
| Mount Thickness (mm):<br>7.5 ±0.1               |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS 2015:<br><a href="#">Compliant</a>             |
| Reach 219:<br><a href="#">Compliant</a>             |
| Certificate of Conformance:<br><a href="#">View</a> |