

34mm Diameter, Prism Mount Metric



Stock #55-012 20+ In Stock

-

1

+

A\$673^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$673.60 each
Qty 5-25	A\$606.24 each
Qty 26-49	A\$572.96 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Rotary & Tip-Tilt

Type:

Cube/Prism

Type of Optics:

Physical & Mechanical Properties

±3

Fine Rotation (°):

±3	Fine Tilt Angle (°):
Threading & Mounting	
20.0	Size of Compatible Optics (mm):
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Precision Fine Movement
 - Holds Prisms up to 30mm
 - Black Anodized Aluminum
 - [Posts](#) and [Post Holders](#) Required for Mounting
- Metric Prism Mounts permit ±3° precision fine movement rotation and ±3° X-Y axes tilt control. These mounts feature durable black anodized aluminum construction and hold prisms up to 30mm. [Posts](#) and [post holders](#) are required for mounting to a breadboard.

Technical Information

Mount Diameter A	Maximum Prism Size B	Base Height C	Maximum Total Mount Height D	Stock No.
34	20	30	76	#55-012
50	30	45	102	#55-013
				