

# 350nm CWL, 40nm FWHM, 50mm Mounted Diameter



Stock **#67-892** 3-5 DAYS

[Additional Bandwidths](#)

- 1 +

**A\$777.60**

ADD TO CART

Qty 1-9

A\$777.60

Qty 10+

A\$698.56

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
50.00 +0.00/-0.25

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

|                                                        |
|--------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>45.0                 |
| <b>Center Wavelength CWL (nm):</b><br>350.00 ±5        |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>±5     |
| <b>Full Width-Half Max FWHM (nm):</b><br>40.00 ±8      |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±8  |
| <b>Minimum Transmission (%):</b><br>>25                |
| <b>Operating Temperature (°C):</b><br>-50 to +50       |
| <b>Coating:</b><br>Traditional Coated                  |
| <b>Surface Quality:</b><br>80-50                       |
| <b>Type:</b><br>Bandpass Filter                        |
| <b>Typical Applications:</b><br>General Filtering      |
| <b>Blocking Wavelength Range (nm):</b><br>200 - 10000  |
| <b>Construction:</b><br>Mounted in Black Anodized Ring |
| <b>Mount Thickness (mm):</b><br>4.9                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |