

355nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #67-893 3-5 DAYS

- 1 + **A\$777.60**

ADD TO CART

Qty 1-9
A\$777.60
Qty 10+
A\$698.56
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm):

45.0
Center Wavelength CWL (nm): 355.00 +2.0/-0.0
Center Wavelength CWL Tolerance (nm): +2.0/-0.0
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): >25
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Nd:YAG Laser Line
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
