

**TECHSPEC® 35mm 488nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#48-877** CLEARANCE 3-5 DAYS

-

1

+

**A\$399.92**

ADD TO CART

Qty 1+

A\$399.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Beam Deviation (arcmin):**  
±3

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
90.00

**Coating Specification:**  
R<sub>abs</sub> <0.25% @ 488nm

**Construction:**  
Cube

|                                                                          |
|--------------------------------------------------------------------------|
| <div>Design Wavelength DWL (nm):<br/>488</div>                           |
| <div>Dimensions (mm):<br/>35.0 x 35.0 x 35.0 ±0.1</div>                  |
| <div>Extinction Ratio:<br/>1000:1</div>                                  |
| <div>P-Polarization Transmission (%):<br/>&gt;95</div>                   |
| <div>S-Polarization Reflection (%):<br/>&gt;99.5</div>                   |
| <div>Substrate: <input type="checkbox"/><br/><a href="#">N-BK7</a></div> |
| <div>Surface Flatness (P-V):<br/>λ/4</div>                               |
| <div>Surface Quality:<br/>40-20</div>                                    |
| <div>Type:<br/>Linear Polarizer</div>                                    |

## Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS:<br/><a href="#">Compliant</a></div>                  |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |