

## 35mm MegaPixel Fixed Focal Length Lens



MegaPixel Fixed Focal Length Lenses

Stock **#64-868** **1 In Stock**

[Similar Products](#)

⊖ 1 ⊕ A\$532<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | A\$532.00 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

**Product Family:**  
MegaPixel Fixed Focal Length Lenses

**Type:**  
Fixed Focal Length Lens

### Physical & Mechanical Properties

**Iris Option:**  
Variable

**Length (mm):**  
38.20

|       |                               |
|-------|-------------------------------|
| 33.50 | Maximum Diameter (mm):        |
| 33.5  | Outer Diameter (mm):          |
| 87.00 | Weight (g):                   |
| 0.00  | Maximum Rear Protrusion (mm): |

## Optical Properties

|              |  |
|--------------|--|
| 44.00        | Field of View @ Min Working Distance (mm): |
| 10.10°       | Horizontal Field of View, 1/2" Sensor:     |
| 11.00        | Maximum Image Circle (mm):                 |
| 35.00        | Focal Length FL (mm):                      |
| 300 - ∞      | Working Distance (mm):                     |
| f/1.4 - f/16 | Aperture (f/#):                            |
| -0.8         | Maximum Distortion (%):                    |
| VIS          | Lens Wavelength Range:                     |

## Sensor

|      |                        |
|------|------------------------|
| 2/3" | Maximum Sensor Format: |
| 6.20 | Pixel Size (µm):       |

## Threading & Mounting

|              |                |
|--------------|----------------|
| M30.5 x 0.50 | Filter Thread: |
| C-Mount      | Mount:         |

## Regulatory Compliance

|                  |                             |
|------------------|-----------------------------|
| Exempt           | RoHS 2015:                  |
| Contains SVHC(s) | Reach 224:                  |
| View             | Certificate of Conformance: |

## Product Details


- Up to 2/3", C-Mount Lens
- Ideal for Machine Vision at an Economical Price
- 5mm to 75mm Focal Length

MegaPixel Fixed Focal Length Lenses are designed for high-resolution imaging. The lenses are ideal for machine vision applications with demanding space constraints. These lenses complement the resolution of many MegaPixel cameras with 1/2" or 2/3" formats. Low distortion and high resolution enable these economically priced lenses to produce sharp, high-contrast images compared to standard CCTV and compact lenses. MegaPixel Fixed Focal Length Lenses are available in focal lengths ranging from 5 to 75mm. Locking screws for the manual iris and focus allow these lenses to be used in high-vibration environments. Typical applications include [factory automation](#), inspection, and macro work.

**Note:** For #64-869 75mm FL Lens, remove focus limit screw to focus past 1.2m.

## Technical Information

### #64-868 35mm Megapixel Fixed Focal Length Lens



(Units in mm)

