

TECHSPEC[®] 35.0mm Dia. x 35.0mm FL, Uncoated, Plano-Convex Lens



Stock **#37-824** 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$64.00

ADD TO CART

Qty 1-9
A\$64.00
Qty 10+
A\$57.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
35.00 +0.0/-0.025

Effective Focal Length EFL (mm):
35.00 @ 587.6nm

Back Focal Length BFL (mm): 30.52
Coating: Uncoated
Substrate:  N-SF11
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.10
Edge Thickness ET (mm): 1.70
Radius R₁ (mm): 27.47
Clear Aperture CA (mm): 34
f#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View