

39mm Outer Dia., Zero Aperture, Stainless Steel Leaves



Zero Series

Stock #57-596 3-5 DAYS



1



A\$164.80

ADD TO CART

Qty 1-4

A\$164.80

Qty 5+

A\$145.44

Volume Pricing

[Request Quote](#)

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
22.0

Outer Diameter (mm):
39.0

Construction:

Anodized Aluminum Alloy, Stainless Steel Leaves

Full Angular Range of Lever (°):
99.00

Lever Diameter (mm):
3

Lever Length (mm):
11.00

Lever Position (mm):
2.50

Number of Leaves:
Two sets of 7

Operating Temperature (°C):
<400

Pin Thread & Pitch:
M1.4 x 0.30mm

Thickness (mm):
5.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)