

3mm Dia. x 12mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-060**

CLEARANCE

3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$31.92

ADD TO CART

Qty 1+

A\$31.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
3.00 +0.00/-0.10

Effective Focal Length EFL (mm):
12.00

Back Focal Length BFL (mm):
11.01

Coating:
Uncoated

Substrate:

N-BK7

Focal Length Tolerance (%): ±1
Centering (arcmin): 6.00
Center Thickness CT (mm): 1.50
Edge Thickness ET (mm): 1.32
Radius R₁ (mm): 6.20
Clear Aperture CA (mm): ≥2.55
f#: 4.00
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View