

[See all 4 Products in Family](#)

3mm Dia. x 12mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-060 CLEARANCE 1 In Stock

[Other Coating Options](#)

1 A\$32.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$32.80 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

3.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

1.50 **Center Thickness CT (mm):**

1.32 Edge Thickness ET (mm):

≥2.55 Clear Aperture CA (mm):

Optical Properties

12.00 Effective Focal Length EFL (mm):

11.01 Back Focal Length BFL (mm):

Uncoated Coating:

N-BK7 Substrate:

±1 Focal Length Tolerance (%):

6.20 Radius R_1 (mm):

4.00 f#:

0.13 Numerical Aperture NA:

Regulatory Compliance

View Certificate of Conformance:

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

