

3mW 850nm, Laboratory Laser Diode



Stock #53-760 3-5 DAYS

- 1 + **A\$896.00**

ADD TO CART

Qty 1+

A\$896.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Output Power (mW):
3 (±5%)

Wavelength (nm):
850.00

Wavelength Tolerance (nm):
±5

Power Supply:
110/240 VAC (included)

Power Requirement: 3.5 - 5 VDC, 60 mA
Beam Size at Nearest Focus (µm): 25
Note: Includes: Users Manual, Power Supply, Warning Label, and Focus Key
Beam Diameter (mm): 4 x2
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): <0.5
Laser Class - CDRH: IIIb
Color: Infrared
Focus Range: 35mm - ∞

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
