

TECHSPEC® 3" Dia. Protected Silver, λ /10 Flat Fused Silica



Stock #01-915-577 [CONTACT US](#)

- 1 + **A\$892.80**

ADD TO CART

Qty 1-10

A\$892.80

Qty 11+

A\$744.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
 λ /10 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 76.20 +0.0/-1.0
Substrate:  Fused Silica (Corning 7980)
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 68.58
Note: Flatness is specified as Peak to Valley
Thickness (mm): 19.10 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference:  0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant