

# 3" LED Ring Light 660nm with Barrel Mount, Strobed

See More by [Advanced Illumination](#)



Stock #83-239 [CONTACT US](#)

⊖ 1 ⊕ **A\$1,297.60**

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| A\$1,297.60 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

**Note:** This item requires accessories for use | [Learn More](#)

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

|                              |
|------------------------------|
| Color:<br>Red                |
| Diameter (mm):<br>85.00      |
| Height (mm):<br>35           |
| Inner Diameter (mm):<br>55.4 |

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Model Number:</b><br>RL 1424B-660-IS                                                                                                                                                                                                     |
| <b>Mount:</b><br>Barrel Mount                                                                                                                                                                                                               |
| <b>Operating Temperature (°C):</b><br>0 to 65                                                                                                                                                                                               |
| <b>Dimensions (mm):</b><br>85 Dia x 35 T                                                                                                                                                                                                    |
| <b>Mounting Threads:</b><br>M4 x 4                                                                                                                                                                                                          |
| <b>Wavelength (nm):</b><br>660.00                                                                                                                                                                                                           |
| <b>Working Distance (inches):</b><br>4.00                                                                                                                                                                                                   |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Light Distribution (%):</b><br>±10 edge to edge (dependent on working distance)                                                                                                                                                          |
| <b>Number of LEDs:</b><br>24.00                                                                                                                                                                                                             |
| <b>Number of Channels:</b><br>1.00                                                                                                                                                                                                          |
| <b>Field Coverage (mm):</b><br>43.18 (1.7 inches)                                                                                                                                                                                           |
| <b>Maximum Trigger Frequency (Hz):</b><br>30.00                                                                                                                                                                                             |
| <b>Strobe Duration (µs):</b><br>30 - 300                                                                                                                                                                                                    |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Ring Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Strobed                                                                                                                                                                                                        |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |