

[All Products](#) / [Imaging Lenses](#) / [Zoom Lenses](#) / [4K Wide Angle Lenses](#)

[See all 21 Products in Family](#)

4-10mm FL CS-Mount, DC Auto Iris, IR Corrected Lens



Image represents #22-799: Design will vary by stock number.

Stock **#22-799** 3-5 DAYS



1



A\$632.00

ADD TO CART

Qty 1+

A\$632.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
DC autoiris

Length (mm):
51.50

Maximum Diameter (mm):
59.0

Weight (g):
78

Horizontal Field of View @ Max Sensor Format: 112° - 44°
Type: Varifocal Lens
Maximum Sensor Format: 1/1.7"
Working Distance (mm): 500 - ∞
Mount: CS-Mount
Aperture (f/#): f/1.4 - Closed
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

