

4" Fiber Optic Diffuse Axial Illuminators



4" Fiber Optic Diffuse Axial Illuminators (#53-381)



Stock **#53-381** 3-5 DAYS

- 1 +

A\$1,272.00

ADD TO CART

Qty 1+
A\$1,272.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Numerical Aperture NA:
0.55 nominal

Fiber Diameter (µm):
50 (0.002" nominal)

Construction:
Black Anodized Aluminum

Packing Fraction (%) : 83% nominal
Transmission Loss : 10% per ft. at 660nm
Type of Illumination : Fiber Optic Light Guide
Geometry : Diffuse Axial

Regulatory Compliance

Reach 174 : Compliant
RoHS : Not Compliant
Certificate of Conformance : View
